

Unilok® Tube Fittings

Unilok® single-ferrule tube fittings provide leak-tight installation when intermixed with Parker® CPI™ fittings, provided they are used in accordance with SSP Fittings' published installation and service recommendations.

To provide a reliable, leak-proof connection in instrumentation and process tubing systems, Unilok tube fittings consist of three precision-machined components: **1Body**, **2Ferrule**, and **3Nut**.

Lifetime Warranty

Unilok tube fittings are covered by a lifetime limited warranty. Visit www.mySSP.com for details.



8250 Boyle Parkway
Twinsburg, OH 44087 U.S.A.
P: 1.330.425.4250



www.mySSP.com

Unilok® Tube Fittings

INSTALLATION INSTRUCTIONS

1. Remove the tube fitting from protective bag.
2. Fully insert the tube into the Unilok tube fitting body, then hand tighten the Unilok nut. See Figure #1
3. While holding the fitting body stable with a back-up wrench, scribe the nut for a reference point and wrench-tighten 1 and 1/4 turns for sizes 1/4" - 1" and 3/4 turn for sizes 1/16" - 3/16". See Figures 2 and 3.

